

Tab. 1 SRB TUBES - DIMENSIONAL RANGE ARTROM STEEL TUBES

WT	mm	5	6	6.35	7.5	10	12.5	15	17.5	20	22.5	25	27.5	30
ID H8	Toler.H8	Length [m]												
50	+0.039/0	5-7	5-7	5-7	5-7	5-7	5-7							
50.8		5-7	5-7	5-7	5-7	5-7	5-7							
55		5-7	5-7	5-7	5-7	5-7	5-7	5-7						
57.15		5-7	5-7	5-7	5-7	5-7	5-7	5-7						
60		5-7	5-7	5-7	5-7	5-7	5-7	5-7						
63		5-7	5-7	5-7	5-7	5-7	5-7	5-7						
63.5	+0.046/0	5-7	5-7	5-7	5-7	5-7	5-7	5-7						
65		5-7	5-7	5-7	5-7	5-7	5-7	5-7						
70		5-7.5	5-7.5	5-7.5	5-7.5	5-7.5	5-7.5	5-7.5	5-7.5					
75		5-7.5	5-7.5	5-7.5	5-7.5	5-7.5	5-7.5	5-7.5	5-7.5					
76.2		5-7.5	5-7.5	5-7.5	5-7.5	5-7.5	5-7.5	5-7.5	5-7.5					
80		5-7.5	5-7.5	5-7.5	5-7.5	5-7.5	5-7.5	5-7.5	5-7.5					
82.55		5-8	5-8	5-8	5-8	5-8	5-8	5-8	5-8					
85		5-8	5-8	5-8	5-8	5-8	5-8	5-8	5-8					
88.9		5-8	5-8	5-8	5-8	5-8	5-8	5-8	5-8					
90		5-8	5-8	5-8	5-8	5-8	5-8	5-8	5-8					
100			5-8.5	5-8.5	5-8.5	5-8.5	5-8.5	5-8.5	5-8.5	5-8.5	5-8.5	5-8.5		
101.6	+0.054/0			5-8.5	5-8.5	5-8.5	5-8.5	5-8.5	5-8.5	5-8.5	5-8.5	5-8.5		
105					5-8.5	5-8.5	5-8.5	5-8.5	5-8.5	5-8.5	5-8.5	5-8.5		
110					5-9	5-9	5-9	5-9	5-9	5-9	5-9	5-9	5-8.5	
114.3					5-9	5-9	5-9	5-9	5-9	5-9	5-9	5-9	5-9	5-8.5
115					5-9	5-9	5-9	5-9	5-9	5-9	5-9	5-9	5-9	5-8.5
120					5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-8.5	5-8.5
125					5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9	5-8.5	5-8.5
127					5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-8.5
130					5-9.5	5-9.5	5-9.5	5-9.5	5-9	5-9	5-9	5-9	5-9	5-8.5
135					5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-8.5	5-8.5
140					5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9	5-9	5-8.5
146.82	+0.063/0				5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9	5-9	5-8.5	5-8
150					5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9	5-8.5	5-8
152.4					5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9.5	5-9	5-8.5	5-8
160					5-10	5-10	5-10	5-10	5-10	5-9	5-9	5-8.5	5-8.5	5-8
170					5-10	5-10	5-10	5-10	5-10	5-9	5-9	5-9	5-8.5	5-8
180					5-10	5-10	5-10	5-9.5	5-9	5-8	5-8	5-8	5-8	5-7
200	+0.072/0				5-10	5-10	5-10	5-10	5-10	5-9	5-8	5-7		

Notes:

- Dimensions with ID = 50 ÷ 65 (marked in gray) are executed on SRBE-7000, and dimensions with ID = 70 ÷ 200 (unmarked) are executed on SRBE-12000
- Dimensions marked in yellow are non-standard